

# Document shredders DAHLE 504



- Convenient desktside document shredder
- Doors open wide for easy emptying of waste container
- Intuitive, user-friendly illuminated control panel with audio signals
- Device shuts down automatically after 30 minutes without use
- Electronic start and stop function controlled by integrated light barrier
- Automatic paper reverse function clears excess paper
- Convenient feeding and reversing function for manual control
- Automatic safety shut-off when the waste container is full or the door is open
- Optical waste level indicator
- High-quality solid steel cutting rollers made of special steel for guaranteed long lifetime
- Pull-out waste container
- Powerful motor ensures high performance and longer run times
- Extremely quiet operation
- Convenient swivel castors, two of which are lockable, with 5 cm ground clearance for greater mobility
- Easy-to-reach main switch on rear of device
- Practical cold-device plug can be detached from document shredder

Article number	40222-04701
Entry width in mm	240
Sheet capacity (80g/sqm)*	5 sheets
Particle size (in mm)	2 x 15 mm
Security levels	P-5/F-2/T-5/E-4
Autom. oiler	-
Oil incl. in ml	50
running time	10min
CDs/DVDs	-
Cards	✓
Paper clips	✓
Waste collection volume (in l)	40
Noise level when idle (db(A))	47
Dimensions H x W x D (mm)	705 x 430 x 350
EAN	4007885247984



\* Maximum number of DIN A4 sheets that can be shredded in a single load under the following conditions: new cutting rollers (oiled if necessary), cold motor, power supply with rated voltage and rated frequency (230V/50Hz; 120V/60Hz). Sheet capacity may be lower and operating noise higher under different conditions. Sheet capacity may also vary due to sheet characteristics and paper feed.

# Document shredders DAHLE 504



Detachable IEC power plug makes the document shredder quick and easy to move from A to B



Separate main switch is located on the rear of the document shredder and completely disconnects it from the mains power supply



P-5 security: recommended, for example, for data media containing secret data